

## Eaton V48M28T7516-US

Eaton General purpose ventilated transformer, Fungus pr, AL windings, DOE 2016, NEMA 2, B+, 75 kVA, Made in USA, Fl/wall mt uprt, 3-ph, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 75 kVA, Not required

<b>PRODUCT NAME</b>	Eaton General purpose ventilated transformer
<b>CATALOG NUMBER</b>	V48M28T7516-US
<b>UPC</b>	786680221286
<b>PRODUCT LENGTH/DEPTH</b>	20 in
<b>PRODUCT HEIGHT</b>	38.5 in
<b>PRODUCT WIDTH</b>	28.5 in
<b>PRODUCT WEIGHT</b>	595 lb
<b>COMPLIANCES</b>	DOE2016 Efficient
<b>CERTIFICATIONS</b>	UL Listed
<b>CATALOG NOTES</b>	10 CFR Part 431 (2016) Efficient



SPECIAL FEATURES	Fungus-resistant varnished core and coil, Made in America
TYPE	Energy-efficient ventilated dry-type transformer
COIL MATERIAL	Aluminum
EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	75 kVA
MOUNTING	Floor or wall, upright only
PHASE	Three-phase
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLTAGE RATING	480 Vac-208Y/120 Vac
ENCLOSURE	NEMA 2
FRAME	B+
INSULATION	220 °C
MATERIAL	Al windings
MODIFICATION 1	Made in America
TAP SIZE	2 at +2.5%, 4 at -2.5%
VOLT AMPERE RATING	75 kVA
WEATHERSHIELD	Not required

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
  
© 2025

Follow us on social media to get the latest product and support information.

