

Eaton V48M28T7516CU-US

Eaton General purpose ventilated transformer, Fungus pr, CU windings, DOE 2016, NEMA 3R, B+, 75 kVA, Made in USA, Fl/wall mt uprt, 3-ph, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at - 2.5%, 75 kVA, Not required

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T7516CU-US
UPC	786680221378
PRODUCT LENGTH/DEPTH	20 in
PRODUCT HEIGHT	38.5 in
PRODUCT WIDTH	28.5 in
PRODUCT WEIGHT	645 lb
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient

SPECIAL FEATURES	Fungus-resistant varnished core and coil, Made in America
TYPE	Energy-efficient ventilated dry-type transformer
COIL MATERIAL	Copper
EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	75 kVA
MOUNTING	Floor or wall, upright only
PHASE	Three-phase
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLTAGE RATING	480 Vac-208Y/120 Vac
ENCLOSURE	NEMA 3R
FRAME	B+
INSULATION	220 °C
MATERIAL	Copper windings
MODIFICATION 1	Made in America
TAP SIZE	2 at +2.5%, 4 at -2.5%
VOLT AMPERE RATING	75 kVA
WEATHERSHIELD	Not required

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

